

Abb.1



Abb.2



Abb.3



### Wall mounting Bracket for 1 large cartridge

Description	Single bracket for 1 aluminium large cartridge, consisting of 2 brackets for wall mounting
Material	Steel, galvanized
Part no.	124535

### Wall mounting system for 1 large cartridge

Description	Wall mounting system for 1 aluminium large cartridge, complete with facility for purging the inlet and outlet connection after each cartridge change. Complete with relief valve, shut-off and purge valves. The components are installed on an aluminium console.
Material	Brass, chrome plated and stainless steel
Connections	Inlet and outlet: 1/4" NPT female
Max. working pressure	10 bar
Part no.	129427

### Wall mounting system for 2 large cartridges

Short text	Double mounting system with purge facility for 2 aluminium large cartridges in combination with 1 Oxisorb® small cartridge for optical load indication.
Description	Double mounting system with optical load indication and facility for purging the inlet and outlet connections after each cartridge change. Complete with relief valve, shut-off valves, purge valves and 1 Oxisorb® small cartridge. The components are installed on an aluminium console.
Material	Brass, chrome plated and stainless steel
Connections	Inlet and outlet: 1/4" NPT female
Max. working pressure	10 bar
Part no.	124531

For compression fittings: see mounting systems for small cartridges